



PD6212 SERIES PRESETS

Crown I-Tech HD Series (2 channel)



Device File: PD6212 R1.I-Tech HD Series.Device

NAME	PRESET	DESCRIPTION	CH 1	CH 2
Passive Full Range Presets				
PD6212/43 Passive IIR	2	PD6212/43 Passive Full Range with IIR processing	PD6212/43 FR IIR	PD6212/43 FR IIR
PD6212/64 Passive IIR	3	PD6212/64 Passive Full Range with IIR processing	PD6212/64 FR IIR	PD6212/64 FR IIR
PD6212/66 Passive IIR	4	PD6212/66 Passive Full Range with IIR processing	PD6212/66 FR IIR	PD6212/66 FR IIR
PD6212/95 Passive IIR	5	PD6212/95 Passive Full Range with IIR processing	PD6212/95 FR IIR	PD6212/95 FR IIR
INTENTIONALLY LEFT BLANK				
Passive Full Range Presets				
PD6212/43 Passive FIR	7	PD6212/43 Passive Full Range with FIR processing	PD6212/43 FR FIR	PD6212/43 FR FIR
PD6212/64 Passive FIR	8	PD6212/64 Passive Full Range with FIR processing	PD6212/64 FR FIR	PD6212/64 FR FIR
PD6212/66 Passive FIR	9	PD6212/66 Passive Full Range with FIR processing	PD6212/66 FR FIR	PD6212/66 FR FIR
PD6212/95 Passive FIR	10	PD6212/95 Passive Full Range with FIR processing	PD6212/95 FR FIR	PD6212/95 FR FIR
INTENTIONALLY LEFT BLANK				
Bi-Amp Full Range Presets				
PD6212/43 Bi-Amp IIR	13	PD6212/43 Bi-Amp Full Range with IIR processing	PD6212/43 LF IIR	PD6212/43 HF IIR
PD6212/64 Bi-Amp IIR	13	PD6212/64 Bi-Amp Full Range with IIR processing	PD6212/64 LF IIR	PD6212/64 HF IIR
PD6212/66 Bi-Amp IIR	14	PD6212/66 Bi-Amp Full Range with IIR processing	PD6212/66 LF IIR	PD6212/66 HF IIR
PD6212/95 Bi-Amp IIR	15	PD6212/95 Bi-Amp Full Range with IIR processing	PD6212/95 LF IIR	PD6212/95 HF IIR
INTENTIONALLY LEFT BLANK				
Bi-Amp Full Range Presets				
PD6212/43 Bi-Amp FIR	17	PD6212/43 Bi-Amp Full Range with FIR processing	PD6212/43 LF FIR	PD6212/43 HF FIR
PD6212/64 Bi-Amp FIR	18	PD6212/64 Bi-Amp Full Range with FIR processing	PD6212/64 LF FIR	PD6212/64 HF FIR
PD6212/66 Bi-Amp FIR	19	PD6212/66 Bi-Amp Full Range with FIR processing	PD6212/66 LF FIR	PD6212/66 HF FIR
PD6212/95 Bi-Amp FIR	20	PD6212/95 Bi-Amp Full Range with FIR processing	PD6212/95 LF FIR	PD6212/95 HF FIR
INTENTIONALLY LEFT BLANK				
Passive Full Range Presets				
PD6212/43 Passive IIR Rotated	22	PD6212/43 Passive Full Range with IIR processing with rotated horns	PD6212/43-H FR IIR	PD6212/43-H FR IIR
PD6212/64 Passive IIR Rotated	23	PD6212/64 Passive Full Range with IIR processing with rotated horns	PD6212/64-H FR IIR	PD6212/64-H FR IIR
PD6212/66 Passive IIR Rotated	24	PD6212/66 Passive Full Range with IIR processing with rotated horns	PD6212/66-H FR IIR	PD6212/66-H FR IIR
PD6212/95 Passive IIR Rotated	25	PD6212/95 Passive Full Range with IIR processing with rotated horns	PD6212/95-H FR IIR	PD6212/95-H FR IIR
INTENTIONALLY LEFT BLANK				
Passive Full Range Presets				
PD6212/43 Passive FIR Rotated	27	PD6212/43 Passive Full Range with FIR processing with rotated horns	PD6212/43-H FR FIR	PD6212/43-H FR FIR
PD6212/64 Passive FIR Rotated	28	PD6212/64 Passive Full Range with FIR processing with rotated horns	PD6212/64-H FR FIR	PD6212/64-H FR FIR
PD6212/66 Passive FIR Rotated	29	PD6212/66 Passive Full Range with FIR processing with rotated horns	PD6212/66-H FR FIR	PD6212/66-H FR FIR
PD6212/95 Passive FIR Rotated	30	PD6212/95 Passive Full Range with FIR processing with rotated horns	PD6212/95-H FR FIR	PD6212/95-H FR FIR
INTENTIONALLY LEFT BLANK				
Bi-Amp Full Range Presets				
PD6212/43 Bi-Amp IIR Rotated	32	PD6212/43 Bi-Amp Full Range with IIR processing with rotated horns	PD6212/43-H LF IIR	PD6212/43-H HF IIR
PD6212/64 Bi-Amp IIR Rotated	33	PD6212/64 Bi-Amp Full Range with IIR processing with rotated horns	PD6212/64-H LF IIR	PD6212/64-H HF IIR
PD6212/66 Bi-Amp IIR Rotated	34	PD6212/66 Bi-Amp Full Range with IIR processing with rotated horns	PD6212/66-H LF IIR	PD6212/66-H HF IIR
PD6212/95 Bi-Amp IIR Rotated	35	PD6212/95 Bi-Amp Full Range with IIR processing with rotated horns	PD6212/95-H LF IIR	PD6212/95-H HF IIR
INTENTIONALLY LEFT BLANK				
Bi-Amp Full Range Presets				
PD6212/43 Bi-Amp FIR Rotated	37	PD6212/43 Bi-Amp Full Range with FIR processing with rotated horns	PD6212/43-H LF FIR	PD6212/43-H HF FIR
PD6212/64 Bi-Amp FIR Rotated	38	PD6212/64 Bi-Amp Full Range with FIR processing with rotated horns	PD6212/64-H LF FIR	PD6212/64-H HF FIR
PD6212/66 Bi-Amp FIR Rotated	39	PD6212/66 Bi-Amp Full Range with FIR processing with rotated horns	PD6212/66-H LF FIR	PD6212/66-H HF FIR
PD6212/95 Bi-Amp FIR Rotated	40	PD6212/95 Bi-Amp Full Range with FIR processing with rotated horns	PD6212/95-H LF FIR	PD6212/95-H HF FIR

NOTES

Passive	Single amp channel will drive a full range speaker with internal crossover in passive mode
Bi-Amp	Two amplifier channels used to individually drive two passbands.
IIR	Infinite Impulse Response, traditional IIR processing
FIR	Finite Impulse Response processing with 7.33ms FIR length above 700z, IIR processing below 700Hz
Rotated	Both horns rotated from standard configuration - Also referred to as -H for Horizontal
FR	Full Range. See Passive
LF	Low Frequency
HF	High Frequency