



PD6322 Presets

Crown I-Tech 4x3500 HD Series, 4 channel

Filename: PD6322 R1.I-Tech 4x3500HD.Device



NAME	PRESET	DESCRIPTION	CH 1	CH 2	CH 3	CH 4
Bi-Amp Full Range Presets						
PD6322/43 Bi-Amp IIR	2	PD6322/43 Bi-Amp Full Range with IIR processing	PD6322/43 LF IIR	PD6322/43 MHF IIR	PD6322/43 LF IIR	PD6322/43 MHF IIR
PD6322/64 Bi-Amp IIR	3	PD6322/64 Bi-Amp Full Range with IIR processing	PD6322/64 LF IIR	PD6322/64 MHF IIR	PD6322/64 LF IIR	PD6322/64 MHF IIR
PD6322/66 Bi-Amp IIR	4	PD6322/66 Bi-Amp Full Range with IIR processing	PD6322/66 LF IIR	PD6322/66 MHF IIR	PD6322/66 LF IIR	PD6322/66 MHF IIR
PD6322/95 Bi-Amp IIR	5	PD6322/95 Bi-Amp Full Range with IIR processing	PD6322/95 LF IIR	PD6322/95 MHF IIR	PD6322/95 LF IIR	PD6322/95 MHF IIR
PD6322/64&95 Bi-Amp IIR	6	PD6322/64 PD6322/95 Bi-Amp Full Range with IIR processing	PD6322/64 LF IIR	PD6322/64 MHF IIR	PD6322/95 LF IIR	PD6322/95 MHF IIR

INTENTIONALLY BLANK

Bi-Amp Full Range Presets						
PD6322/43 Bi-Amp FIR	8	PD6322/43 Bi-Amp Full Range with FIR processing	PD6322/43 LF FIR	PD6322/43 MHF FIR	PD6322/43 LF FIR	PD6322/43 MHF FIR
PD6322/64 Bi-Amp FIR	9	PD6322/64 Bi-Amp Full Range with FIR processing	PD6322/64 LF FIR	PD6322/64 MHF FIR	PD6322/64 LF FIR	PD6322/64 MHF FIR
PD6322/66 Bi-Amp FIR	10	PD6322/66 Bi-Amp Full Range with FIR processing	PD6322/66 LF FIR	PD6322/66 MHF FIR	PD6322/66 LF FIR	PD6322/66 MHF FIR
PD6322/95 Bi-Amp FIR	11	PD6322/95 Bi-Amp Full Range with FIR processing	PD6322/95 LF FIR	PD6322/95 MHF FIR	PD6322/95 LF FIR	PD6322/95 MHF FIR
PD6322/64&95 Bi-Amp FIR	12	PD6322/64 PD6322/95 Bi-Amp Full Range with FIR processing	PD6322/64 LF FIR	PD6322/64 MHF FIR	PD6322/95 LF FIR	PD6322/95 MHF FIR

INTENTIONALLY BLANK

Tri-Amp Full Range Presets						
PD6322/43 Tri-Amp IIR	14	PD6322/43 Tri-Amp Full Range with IIR processing	PD6322/43 LF IIR	PD6322/43 LF IIR	PD6322/43 MF IIR	PD6322/43 HF IIR
PD6322/64 Tri-Amp IIR	15	PD6322/64 Tri-Amp Full Range with IIR processing	PD6322/64 LF IIR	PD6322/64 LF IIR	PD6322/64 MF IIR	PD6322/64 HF IIR
PD6322/66 Tri-Amp IIR	16	PD6322/66 Tri-Amp Full Range with IIR processing	PD6322/66 LF IIR	PD6322/66 LF IIR	PD6322/66 MF IIR	PD6322/66 HF IIR
PD6322/95 Tri-Amp IIR	17	PD6322/95 Tri-Amp Full Range with IIR processing	PD6322/95 LF IIR	PD6322/95 LF IIR	PD6322/95 MF IIR	PD6322/95 HF IIR

INTENTIONALLY BLANK

Tri-Amp Full Range Presets						
PD6322/43 Tri-Amp FIR	19	PD6322/43 Tri-Amp Full Range with FIR processing	PD6322/43 LF FIR	PD6322/43 LF FIR	PD6322/43 MF FIR	PD6322/43 HF FIR
PD6322/64 Tri-Amp FIR	20	PD6322/64 Tri-Amp Full Range with FIR processing	PD6322/64 LF FIR	PD6322/64 LF FIR	PD6322/64 MF FIR	PD6322/64 HF FIR
PD6322/66 Tri-Amp FIR	21	PD6322/66 Tri-Amp Full Range with FIR processing	PD6322/66 LF FIR	PD6322/66 LF FIR	PD6322/66 MF FIR	PD6322/66 HF FIR
PD6322/95 Tri-Amp FIR	22	PD6322/95 Tri-Amp Full Range with FIR processing	PD6322/95 LF FIR	PD6322/95 LF FIR	PD6322/95 MF FIR	PD6322/95 HF FIR

INTENTIONALLY BLANK

Bi-Amp Full Range Presets						
PD6322/43 Bi-Amp IIR Rotated	24	PD6322/43 Bi-Amp Full Range with IIR processing with rotated horns	PD6322/43-H LF IIR	PD6322/43-H MHF IIR	PD6322/43-H LF IIR	PD6322/43-H MHF IIR
PD6322/64 Bi-Amp IIR Rotated	25	PD6322/64 Bi-Amp Full Range with IIR processing with rotated horns	PD6322/64-H LF IIR	PD6322/64-H MHF IIR	PD6322/64-H LF IIR	PD6322/64-H MHF IIR
PD6322/66 Bi-Amp IIR Rotated	26	PD6322/66 Bi-Amp Full Range with IIR processing with rotated horns	PD6322/66-H LF IIR	PD6322/66-H MHF IIR	PD6322/66-H LF IIR	PD6322/66-H MHF IIR
PD6322/95 Bi-Amp IIR Rotated	27	PD6322/95 Bi-Amp Full Range with IIR processing with rotated horns	PD6322/95-H LF IIR	PD6322/95-H MHF IIR	PD6322/95-H LF IIR	PD6322/95-H MHF IIR
PD6322/64&95 Bi-Amp IIR Rotated	28	PD6322/64 PD6322/95 Bi-Amp Full Range with IIR processing with rotated horns	PD6322/64-H LF IIR	PD6322/64-H MHF IIR	PD6322/95-H LF IIR	PD6322/95-H MHF IIR

INTENTIONALLY BLANK

Bi-Amp Full Range Presets						
PD6322/43 Bi-Amp FIR Rotated	30	PD6322/43 Bi-Amp Full Range with FIR processing with rotated horns	PD6322/43-H LF FIR	PD6322/43-H MHF FIR	PD6322/43-H LF FIR	PD6322/43-H MHF FIR
PD6322/64 Bi-Amp FIR Rotated	31	PD6322/64 Bi-Amp Full Range with FIR processing with rotated horns	PD6322/64-H LF FIR	PD6322/64-H MHF FIR	PD6322/64-H LF FIR	PD6322/64-H MHF FIR
PD6322/66 Bi-Amp FIR Rotated	32	PD6322/66 Bi-Amp Full Range with FIR processing with rotated horns	PD6322/66-H LF FIR	PD6322/66-H MHF FIR	PD6322/66-H LF FIR	PD6322/66-H MHF FIR
PD6322/95 Bi-Amp FIR Rotated	33	PD6322/95 Bi-Amp Full Range with FIR processing with rotated horns	PD6322/95-H LF FIR	PD6322/95-H MHF FIR	PD6322/95-H LF FIR	PD6322/95-H MHF FIR
PD6322/64&95 Bi-Amp FIR Rotated	34	PD6322/64 PD6322/95 Bi-Amp Full Range with FIR processing with rotated horns	PD6322/64-H LF FIR	PD6322/64-H MHF FIR	PD6322/95-H LF FIR	PD6322/95-H MHF FIR

INTENTIONALLY BLANK

Tri-Amp Full Range Presets						
PD6322/43 Tri-Amp IIR Rotated	36	PD6322/43 Tri-Amp Full Range with IIR processing with rotated horns	PD6322/43-H LF IIR	PD6322/43-H LF IIR	PD6322/43-H MF IIR	PD6322/43-H HF IIR
PD6322/64 Tri-Amp IIR Rotated	37	PD6322/64 Tri-Amp Full Range with IIR processing with rotated horns	PD6322/64-H LF IIR	PD6322/64-H LF IIR	PD6322/64-H MF IIR	PD6322/64-H HF IIR
PD6322/66 Tri-Amp IIR Rotated	38	PD6322/66 Tri-Amp Full Range with IIR processing with rotated horns	PD6322/66-H LF IIR	PD6322/66-H LF IIR	PD6322/66-H MF IIR	PD6322/66-H HF IIR
PD6322/95 Tri-Amp IIR Rotated	39	PD6322/95 Tri-Amp Full Range with IIR processing with rotated horns	PD6322/95-H LF IIR	PD6322/95-H LF IIR	PD6322/95-H MF IIR	PD6322/95-H HF IIR

INTENTIONALLY BLANK

Tri-Amp Full Range Presets						
PD6322/43 Tri-Amp FIR Rotated	41	PD6322/43 Tri-Amp Full Range with FIR processing with rotated horns	PD6322/43-H LF FIR	PD6322/43-H LF FIR	PD6322/43-H MF FIR	PD6322/43-H HF FIR
PD6322/64 Tri-Amp FIR Rotated	42	PD6322/64 Tri-Amp Full Range with FIR processing with rotated horns	PD6322/64-H LF FIR	PD6322/64-H LF FIR	PD6322/64-H MF FIR	PD6322/64-H HF FIR
PD6322/66 Tri-Amp FIR Rotated	43	PD6322/66 Tri-Amp Full Range with FIR processing with rotated horns	PD6322/66-H LF FIR	PD6322/66-H LF FIR	PD6322/66-H MF FIR	PD6322/66-H HF FIR
PD6322/95 Tri-Amp FIR Rotated	44	PD6322/95 Tri-Amp Full Range with FIR processing with rotated horns	PD6322/95-H LF FIR	PD6322/95-H LF FIR	PD6322/95-H MF FIR	PD6322/95-H HF FIR

NOTES

Bi-Amp	Two amplifier channels drive loudspeaker in Bi-Amp Mode: LF driven separately from MHF with internal passive crossover.
Tri-Amp	Three amplifier channels drive loudspeaker in Tri-Amp Mode: Each passband is driven with discrete amplifier channel.
IIR	Infinite Impulse Response processing.
FIR	Finite Impulse Response processing with 7.33ms FIR length.
Rotated	Both horns rotated for horizontal coverage.
-H	Rotated horns, see above
LF	Low Frequency
MF	Mid Frequency
HF	High Frequency
MHF	Mid-High Frequency with internal passive crossover