



PD6322 SERIES PRESETS

Crown I-Tech HD Series (2 channel)



Device File: PD6322 Tri-Amp R1.I-Tech HD Series.Device

NAME	PRESET	DESCRIPTION	CH 1	CH 2
Tri-Amp Full Range Presets				
PD6322/43 TA LF/LF IIR	2	PD6322/43 Tri-Amp Full Range LF/LF with IIR processing	PD6322/43 LF IIR	PD6322/43 LF IIR
PD6322/43 TA MF/HF IIR	3	PD6322/43 Tri-Amp Full Range MF/HF with IIR processing	PD6322/43 MF IIR	PD6322/43 HF IIR
PD6322/64 TA LF/LF IIR	4	PD6322/64 Tri-Amp Full Range LF/LF with IIR processing	PD6322/64 LF IIR	PD6322/64 LF IIR
PD6322/64 TA MF/HF IIR	5	PD6322/64 Tri-Amp Full Range MF/HF with IIR processing	PD6322/64 MF IIR	PD6322/64 HF IIR
PD6322/66 TA LF/LF IIR	6	PD6322/66 Tri-Amp Full Range LF/LF with IIR processing	PD6322/66 LF IIR	PD6322/66 LF IIR
PD6322/66 TA MF/HF IIR	7	PD6322/66 Tri-Amp Full Range MF/HF with IIR processing	PD6322/66 MF IIR	PD6322/66 HF IIR
PD6322/95 TA LF/LF IIR	8	PD6322/95 Tri-Amp Full Range LF/LF with IIR processing	PD6322/95 LF IIR	PD6322/95 LF IIR
PD6322/95 TA MF/HF IIR	9	PD6322/95 Tri-Amp Full Range MF/HF with IIR processing	PD6322/95 MF IIR	PD6322/95 HF IIR
INTENTIONALLY BLANK				
TA Full Range Presets				
PD6322/43 TA LF/LF FIR	11	PD6322/43 Tri-Amp Full Range LF/LF with FIR processing	PD6322/43 LF FIR	PD6322/43 LF FIR
PD6322/43 TA MF/HF FIR	12	PD6322/43 Tri-Amp Full Range MF/HF with FIR processing	PD6322/43 MF FIR	PD6322/43 HF FIR
PD6322/64 TA LF/LF FIR	13	PD6322/64 Tri-Amp Full Range LF/LF with FIR processing	PD6322/64 LF FIR	PD6322/64 LF FIR
PD6322/64 TA MF/HF FIR	14	PD6322/64 Tri-Amp Full Range MF/HF with FIR processing	PD6322/64 MF FIR	PD6322/64 HF FIR
PD6322/66 TA LF/LF FIR	15	PD6322/66 Tri-Amp Full Range LF/LF with FIR processing	PD6322/66 LF FIR	PD6322/66 LF FIR
PD6322/66 TA MF/HF FIR	16	PD6322/66 Tri-Amp Full Range MF/HF with FIR processing	PD6322/66 MF FIR	PD6322/66 HF FIR
PD6322/95 TA LF/LF FIR	17	PD6322/95 Tri-Amp Full Range LF/LF with FIR processing	PD6322/95 LF FIR	PD6322/95 LF FIR
PD6322/95 TA MF/HF FIR	18	PD6322/95 Tri-Amp Full Range MF/HF with FIR processing	PD6322/95 HF FIR	PD6322/95 MF FIR
INTENTIONALLY BLANK				
TA Full Range Presets				
PD6322/43 TA LF/LF IIR Rotated	20	PD6322/43 Tri-Amp Full Range LF/LF with IIR processing with rotated horns	PD6322/43-H LF IIR	PD6322/43-H LF IIR
PD6322/43 TA MF/HF IIR Rotated	21	PD6322/43 Tri-Amp Full Range MF/HF with IIR processing with rotated horns	PD6322/43-H MF IIR	PD6322/43-H HF IIR
PD6322/64 TA LF/LF IIR Rotated	22	PD6322/64 Tri-Amp Full Range LF/LF with IIR processing with rotated horns	PD6322/64-H LF IIR	PD6322/64-H LF IIR
PD6322/64 TA MF/HF IIR Rotated	23	PD6322/64 Tri-Amp Full Range MF/HF with IIR processing with rotated horns	PD6322/64-H MF IIR	PD6322/64-H HF IIR
PD6322/66 TA LF/LF IIR Rotated	24	PD6322/66 Tri-Amp Full Range LF/LF with IIR processing with rotated horns	PD6322/66-H LF IIR	PD6322/66-H LF IIR
PD6322/66 TA MF/HF IIR Rotated	25	PD6322/66 Tri-Amp Full Range MF/HF with IIR processing with rotated horns	PD6322/66-H MF IIR	PD6322/66-H HF IIR
PD6322/95 TA LF/LF IIR Rotated	26	PD6322/95 Tri-Amp Full Range LF/LF with IIR processing with rotated horns	PD6322/95-H LF IIR	PD6322/95-H LF IIR
PD6322/95 TA MF/HF IIR Rotated	27	PD6322/95 Tri-Amp Full Range MF/HF with IIR processing with rotated horns	PD6322/95-H MF IIR	PD6322/95-H HF IIR
INTENTIONALLY BLANK				
TA Full Range Presets				
PD6322/43 TA LF/LF FIR Rotated	29	PD6322/43 Tri-Amp Full Range LF/LF with FIR processing with rotated horns	PD6322/43-H LF FIR	PD6322/43-H LF FIR
PD6322/43 TA MF/HF FIR Rotated	30	PD6322/43 Tri-Amp Full Range MF/HF with FIR processing with rotated horns	PD6322/43-H MF FIR	PD6322/43-H HF FIR
PD6322/64 TA LF/LF FIR Rotated	31	PD6322/64 Tri-Amp Full Range LF/LF with FIR processing with rotated horns	PD6322/64-H LF FIR	PD6322/64-H LF FIR
PD6322/64 TA MF/HF FIR Rotated	32	PD6322/64 Tri-Amp Full Range MF/HF with FIR processing with rotated horns	PD6322/64-H MF FIR	PD6322/64-H HF FIR
PD6322/66 TA LF/LF FIR Rotated	33	PD6322/66 Tri-Amp Full Range LF/LF with FIR processing with rotated horns	PD6322/66-H LF FIR	PD6322/66-H LF FIR
PD6322/66 TA MF/HF FIR Rotated	34	PD6322/66 Tri-Amp Full Range MF/HF with FIR processing with rotated horns	PD6322/66-H MF FIR	PD6322/66-H HF FIR
PD6322/95 TA LF/LF FIR Rotated	35	PD6322/95 Tri-Amp Full Range LF/LF with FIR processing with rotated horns	PD6322/95-H LF FIR	PD6322/95-H LF FIR
PD6322/95 TA MF/HF FIR Rotated	36	PD6322/95 Tri-Amp Full Range MF/HF with FIR processing with rotated horns	PD6322/95-H MF FIR	PD6322/95-H HF FIR

NOTES

TA	Tri-Amp: three amplifier channels used to individually drive three passbands.
IIR	Infinite Impulse Response, traditional IIR processing
FIR	Finite Impulse Response processing with 7.33ms FIR length above 700z, IIR processing below 700Hz
Rotated	Both horns rotated from standard configuration - Also referred to as -H for Horizontal
LF	Low Frequency
MF	Mid Frequency
HF	High Frequency